

Tubo Para Forno De Alumina (Al₂O₃) - Alta Temperatura

Número do item: KM-C06



Introduction

O tubo de forno de alumina de alta temperatura combina as vantagens da alta dureza da alumina, boa inércia química e aço, e tem excelente resistência ao desgaste, resistência ao choque térmico e resistência ao choque mecânico.

[Saiba mais](#)

exterior 4mm interior 2mm (1 metro)	exterior 12mm interior 8mm (1 metro)	exterior 25mm interior 19mm (1 metro)	exterior 45mm interior 36mm (1 metro)	exterior 70 mm interior 60 mm (1 metro)
exterior 5mm interior 3mm (1 metro)	exterior 16mm interior 11mm (1 metro)	exterior 30mm interior 24mm (1 metro)	exterior 50mm interior 40mm (1 metro)	exterior 80mm interior 70mm (1 metro)
exterior 6mm interior 4mm (1 metro)	exterior 18mm interior 13mm (1 metro)	exterior 32mm interior 26mm (1 metro)	exterior 55mm interior 45mm (1 metro)	exterior 90mm interior 80mm (1 metro)
exterior 8mm interior 5mm (1 metro)	exterior 20mm interior 15mm (1 metro)	exterior 35mm interior 28mm (1 metro)	exterior 60mm interior 50mm (1 metro)	90mm exterior 100mm interior (1 metro)
exterior 10mm interior 6mm (1 metro)	exterior 22mm interior 16mm (1 metro)	exterior 40mm interior 32mm (1 metro)	exterior 65mm interior 55mm (1 metro)	